

DentalPRO Xtract 200

DUST AND FUME EXTRACTION CABINET FOR **DENTAL LABORATORY** APPLICATIONS.

BOFA's DentalPRO Xtract 200 dust and fume extraction cabinet is designed for the effective removal of potentially harmful dust and fumes generated during dental hand finishing or Monomer mixing applications.

This unit is ideally suited to manual bench top applications and provides technicians the flexibility to work without restriction in the knowledge that dust particles and fumes are being effectively removed to maintain a safe working environment.

This system combines maximum technician protection in a small footprint, with scalable and flexible options.


STANDARD FFATURES:

- Easily replaced screen protector ensures clear visibility at all times
- Internal LED strip light
- Side entry grommets for mains powered hand finishing units
- Removable collection tray
- Strong rigid construction
- Powder coated white

OPTIONAL FEATURES:


- DentalPRO 250 filtration system
- DentalPRO 400 filtration system
- DentalPRO Mono filtration system








| TECHNICAL DATA - D | entalPRO Xtract 200 | | |
|---------------------------|---------------------|---------------------|--|
| | EU | US | |
| Dimensions (HxWxD) | 350 x 540 x 360mm | 13.4 × 21.3 × 14.7" | |
| Opening Dimensions (HxW) | 315 x 540mm | 12.4 x 21.3" | |
| Recommended Face Velocity | 0.5m/s | 150 f/min | |
| Approvals | CE | | |







CABINET





EXTRACTION SYSTEM

| A. DENTALF | PRO 400 | | | |
|---|--|------------|-------------|----|
| Model | Option | Voltage | Part Number | |
| | | | DL0944A0000 | P. |
| DentalPRO 400 Powder coated unit Twin port 75mm lid | 24V Stop / Start Override Silter Change Signal | 90V - 257V | DL0944A0001 | |
| B. UNIT OP | TIONS | | | |
| Description | | | Part Number | - |
| Foot switch (ON / OF | FF Operation) | | A1070184 | |
| | | | () | |

| Model | Voltage | Part Number | |
|--|---------|-------------|---------|
| DentalPRO 250 | 230V | DL0142A0000 | |
| Powder coated unit Single port 75mm lid | 115V | DL0141A0000 | |
| DentalPRO 250 Powder coated unit | 230V | DL0142A8000 | |
| Single port 75mm 90° spigot lid | 115V | DL0141A8000 | |
| D. UNIT OPTION | | | Constay |
| Description | | Part Number | |
| Foot switch | | A1070184 | |

| Model | Voltage | Part Number | |
|--|---------|-------------|---|
| DentalPRO Mono | 230V | DL2043A0000 | |
| Powder coated unit Single port 75mm lid | 115V | DL2041A0000 | E |





Unit 9, Claylands Business park Claylands Road, Bishops Waltham Southampton, Hampshire, SO32 1QD

